



MultiMaster MM 700 Max Top Verzija 0, Tip: 71293663



Podaci za narudžbu

Broj narudžbe	077807 71293663
GTIN	4014586895291
Razred artikla	03F

Opis

Izvedba:

Oscilirajući alati u tri različite klase snage (SuperCut, MultiMaster, MultiTalent) novije izvedbe sa **prihvatom alata Starlock** (poboljšani prijenos snage za do 35 % više napretka u radu) vodeći su na tržištu.

- **Gotovo neograničene mogućnosti primjene (piljenje, brušenje, struganje, rezanje, turpijanje) oscilirajućim pokretima (minimalno stvaranje prašine).**
- **Nestupnjevita elektronička regulacija broja okretaja za optimalan rad.**
- **Maksimalna kvaliteta i stabilnost zahvaljujući metalnom pogonu i kontinuiranoj primjeni kugličnih i igličastih ležajeva.**
- **Optimalno rukovanje zahvaljujući ergonomskom dizajnu s mekanim umecima i maloj težini.**

Najprikladniji MultiTool za brzi rad pri radovima na nadogradnji i obnavljanju s listom pile od bimetala za drvo, metal i plastiku. Zahvaljujući StarlockMax prijvatu za alat ostvarujete pristup na 180 alata marke FEIN u razredima izvedbe Starlock, StarlockPlus i StarlockMax.

Dio isporuke:

2× zakrivljeni listovi pile E-Cut Standard (35 mm), 2× zakrivljeni listovi pile E-Cut Standard (65 mm), 1× list pile E-Cut Precision (35 mm), 1× list pile E-Cut Precision (65 mm), 1× list pile E-Cut Long-Life (10 mm), 2× listovi pile E-Cut Long-Life (35 mm), 1× list pile E-Cut Long-Life (32 mm), 1× list pile E-Cut Long-Life (42 mm), 1× list pile E-Cut Carbide Pro (32 mm), 1× segmentirani list pile (Ø 85 mm), 1× segmentirani list pile od tvrdog metala, 1× turpija od tvrdog metala (oblik trokuta), 1× lopatica, 1× nož za rezanje, oblik gljive, 1× višenamjenski nož, 1× perforirana brusna ploča, po 10× perforiranih brusnih listova (K 60, 80, 120, 180), 1× usisavač, 1× plastični kofer za alat (L-Boxx 136). Verzija 0 (bez akumulatora).

Tehnički opis

Opskrba energijom	Mrežni pogon
Oznaka proizvođača	MULTIMASTER AMM 700 MAX TOP AS 18V/-
Napon baterije	18 V
Broj sadržanih baterija	0
Broj vibracija	10 - 19500 min ⁻¹
Vrsta baterije	Litij-ionska baterija
Pakiranje	Transportni kovčeg
odgovarajuća baterija – dobavljač/tip baterije/napon	Bosch 18 V
Vrsta proizvoda	Oscilatori

Pribor

HM brusna pločica, trokutasti oblik	077888
E-Cut list pile, standardno, 5-dijelno širina reza 35 mm	077840 35
Segmentirani rezni list, dijamant, 1,2 mm Ø lista pile 90 mm	077830 90
Rezni list, Bi-metal HSS Ø lista pile 85 mm	077838 85
Rezni list, potpuno HSS Ø lista pile 85 mm	077834 85
E-Cut-list pile, Bi-metal, Fine širina reza 30 mm	077857 30
E-Cut-list pile, Bi-metal, Long-Life širina reza 32 mm	077884 32
E-Cut-list pile, Diamant, 1,2 mm	077887
E-Cut list pile, standardan, zaobljen širina reza 50 mm	077870 50
E-Cut-garnitura lista pile, MiniCut3-dijelna izvedba SET	077859 SET
E-Cut-list pile, Bi-metal, Long-Life širina reza 42 mm	077884 42
Segmentirani list pile, HM Ø lista pile 90 mm	077828 90
E-Cut-list pile, Standard širina reza 35 mm	077844 35

E-Cut-list pile, Diamant, SLP prihvatnik širina reza 35 mm	077849 35
Segmentirani rezni list, dijamant, 2,2 mm Ø lista pile 75 mm	077867 75
E-Cut list pile, standardno, 5-dijelno širina reza 65 mm	077840 65
Rezni list, Bi-metal HSS Ø lista pile 100 mm	077838 100
Segmentirani rezni list, HM, 2,2 mm Ø lista pile 75 mm	077865 75
Segmentirani rezni list, HM, 2,2 mm Ø lista pile 90 mm	077865 90
List pile E-Cut, Carbide Pro širina reza 35 mm	077893 35
E-Cut-list pile, Standard širina reza 65 mm	077844 65
MultiMaster MM 700 Max TopAkumulator tip 71293462	077805 71293462
E-Cut-list pile, HM, SLP prihvatnik širina reza 35 mm	077858 35
Rezni list, Bi-metal HSS, 5-dijelni Ø lista pile 85 mm	077839 85
E-Cut-list pile, Bi-metal, Universal širina reza 44 mm	077856 44
Segmentirani rezni list, dijamant Ø lista pile 90 mm	077868 90
List pile E-Cut, Carbide-Pro širina reza 35 mm	077891 35
Segmentirani rezni list, dijamant, 2,2 mm Ø lista pile 90 mm	077867 90
Segmentirani list pile, Bi-metall HSS Ø lista pile 100 mm	077827 100
E-Cut list pile, standardan, zaobljen širina reza 35 mm	077870 35
Rezni list, Bi-metal HSS, 5-dijelni Ø lista pile 100 mm	077839 100
E-Cut-list pile, Diamant, 2,2 mm	077886
E-Cut-list pile, Bi-metal, Long-Life širina reza 20 mm	077847 20
E-Cut-list pile, Diamant širina reza 44 mm	077885 44
Segmentirani rezni list, HM, 1,2 mm Ø lista pile 75 mm	077829 75
Segmentirani rezni list, HM, 1,2 mm Ø lista pile 90 mm	077829 90
E-Cut-list pile, Bi-metal, Precision širina reza 35 mm	077850 35
E-Cut-garnitura lista pile, drvo + metal6-dijelna izvedba SET	077848 SET
Segmentirani rezni list, potpuno HSS Ø lista pile 85 mm	077836 85
Rezni list, potpuno HSS, 5-dijelni Ø lista pile 85 mm	077835 85
	077830 75

Segmentirani rezni list, dijamant, 1,2 mm Ø lista pile 75 mm

Litij-ionski akumulator ProCore tip akumulatora, napon akumulatora C18 V

073856 C18

Garnitura aku punjača ProCore tip akumulatora, napon akumulatora C18 V

073867 C18