

**Pritezni vijak****Podaci za narudžbu**

| | |
|----------------|---------------|
| Broj narudžbe | 272520 |
| GTIN | 4045197142825 |
| Razred artikla | 29Y |

Opis

Pritezni vijak

Tehnički opis

| | |
|---------------|----------|
| Pogon | TX8 |
| Navoji | M2,6 |
| Duljina D (L) | 6,5 mm |
| Stezni moment | 1,02 N·m |