

**Garnitura vijaka za izmjenjive rezne pločice 10-dijelna, Tip: 1****Podaci za narudžbu**

Broj narudžbe	269435 1
GTIN	4045197959775
Razred artikla	29Y

Opis

Garnitura vijaka za izmjenjive rezne pločice 10-dijelna 1 Pogon: TX20

Navoji: M4,5×0,75

Duljina D (L): 10,5 mm

Stezni moment: 4 - 5 N·m

Tehnički opis

Pogon	TX20
Stezni moment	4 - 5 N·m
Navoji	M4,5×0,75
Duljina D (L)	10,5 mm