

**Garnitura vijaka za izmjenjive rezne pločice 10-dijelna, Tip: 4****Podaci za narudžbu**

Broj narudžbe	269435 4
GTIN	4045197959850
Razred artikla	29Y

**Opis**

Garnitura vijaka za izmjenjive rezne pločice 10-dijelna 4 Pogon: TX15

Navoji: M4

Duljina D (L): 10,5 mm

Stezni moment: 3 N·m

**Tehnički opis**

Duljina D (L)	10,5 mm
Navoji	M3,5
Pogon	TX15
Stezni moment	3 N·m