



## Ultradźwiękowe urządzenie do czyszczenia Elmasonic Select, Typ: 3



### Dane zamówienia

Numer katalogowy

082000 3

GTIN

Klasa artykułu

04S

### Opis

#### Wykonanie:

The ultrasonic cleaning devices from the Elmasonic Select series are powerful and individual.

- **5 ultrasonic modes.**
- **4 individual cleaning programs can be saved.**
- **Clear display showing all relevant cleaning parameters.**
- **Acoustic and visual feedback about the operating status.**
- **Tray made of drawn stainless steel**

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

oznaczenie producenta: Select 30

pojemność: 2,7 l

długość urządzenia: 305 mm

szerokość urządzenia: 170 mm

długość kosza wsadowego: 195 mm

Szerokość kosza wsadowego: 105 mm

### Opis techniczny

oznaczenie producenta	Select 30
wysokość pojemnika do czyszczenia	95 mm
napięcie znamionowe	220 - 240 V
długość kosza wsadowego	195 mm
długość urządzenia	305 mm
zasilanie energią	Zasilanie sieciowe
szerokość urządzenia	170 mm
Szerokość kosza wsadowego	105 mm
moc grzewcza	200 W
masa	3,6 kg
Moc szczytowa ultradźwięków	480 W
pojemność	2,7 l
zalecana objętość robocza	1,6 l
Rodzaj produktu	Ultradźwiękowe urządzenie do czyszczenia