



## Ultradźwiękowe urządzenie do czyszczenia Elmasonic Select, Typ: 6



### Dane zamówienia

Numer katalogowy

082000 6

GTIN

Klasa artykułu

04S

### Opis

#### Wykonanie:

The ultrasonic cleaning devices from the Elmasonic Select series are powerful and individual.

- **5 ultrasonic modes.**
- **4 individual cleaning programs can be saved.**
- **Clear display showing all relevant cleaning parameters.**
- **Acoustic and visual feedback about the operating status.**
- **Tray made of drawn stainless steel**

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

pojemność: 5,9 l

długość urządzenia: 370 mm

szerokość urządzenia: 210 mm

długość kosza wsadowego: 225 mm

Szerokość kosza wsadowego: 115 mm

wysokość pojemnika do czyszczenia: 145 mm

### Opis techniczny

Szerokość kosza wsadowego	115 mm
długość urządzenia	370 mm
zasilanie energią	Zasilanie sieciowe
wysokość pojemnika do czyszczenia	145 mm
Moc szczytowa ultradźwięków	600 W
moc grzewcza	400 W
masa	5,2 kg
oznaczenie producenta	Select 60
szerokość urządzenia	210 mm
długość kosza wsadowego	225 mm
napięcie znamionowe	220 - 240 V
pojemność	5,9 l
zalecana objętość robocza	4,3 l
Rodzaj produktu	Ultradźwiękowe urządzenie do czyszczenia