



Ultradźwiękowe urządzenie do czyszczenia Elmasonic Select, Typ: 18



Dane zamówienia

| | |
|------------------|-----------|
| Numer katalogowy | 082000 18 |
| GTIN | |
| Klasa artykułu | 04S |

Opis

Wykonanie:

The ultrasonic cleaning devices from the Elmasonic Select series are powerful and individual.

- **5 ultrasonic modes.**
- **4 individual cleaning programs can be saved.**
- **Clear display showing all relevant cleaning parameters.**
- **Acoustic and visual feedback about the operating status.**
- **Tray made of drawn stainless steel**

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

pojemność: 17,8 l

długość urządzenia: 405 mm

szerokość urządzenia: 360 mm

długość kosza wsadowego: 280 mm

Szerokość kosza wsadowego: 250 mm

wysokość pojemnika do czyszczenia: 195 mm

Opis techniczny

| | |
|-----------------------------------|--|
| oznaczenie producenta | Select 180 |
| Moc szczytowa ultradźwięków | 800 W |
| szerokość urządzenia | 360 mm |
| wysokość pojemnika do czyszczenia | 195 mm |
| długość urządzenia | 405 mm |
| napięcie znamionowe | 220 - 240 V |
| Szerokość kosza wsadowego | 250 mm |
| długość kosza wsadowego | 280 mm |
| masa | 10,2 kg |
| moc grzewcza | 800 W |
| zasilanie energią | Zasilanie sieciowe |
| pojemność | 17,8 l |
| zalecana objętość robocza | 14,2 l |
| Rodzaj produktu | Ultradźwiękowe urządzenie do czyszczenia |