



## Ultradźwiękowe urządzenie do czyszczenia Elmasonic Select, Typ: 12



### Dane zamówienia

Numer katalogowy

082000 12

GTIN

Klasa artykułu

04S

### Opis

#### Wykonanie:

The ultrasonic cleaning devices from the Elmasonic Select series are powerful and individual.

- **5 ultrasonic modes.**
- **4 individual cleaning programs can be saved.**
- **Clear display showing all relevant cleaning parameters.**
- **Acoustic and visual feedback about the operating status.**
- **Tray made of drawn stainless steel**

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

pojemność: 12,9 l

długość urządzenia: 380 mm

szerokość urządzenia: 300 mm

długość kosza wsadowego: 250 mm

Szerokość kosza wsadowego: 190 mm

wysokość pojemnika do czyszczenia: 195 mm

### Opis techniczny

masa	7,7 kg
napięcie znamionowe	220 - 240 V
zasilanie energią	Zasilanie sieciowe
szerokość urządzenia	300 mm
długość kosza wsadowego	250 mm
oznaczenie producenta	Select 120
wysokość pojemnika do czyszczenia	195 mm
moc grzewcza	800 W
Szerokość kosza wsadowego	190 mm
długość urządzenia	380 mm
Moc szczytowa ultradźwięków	800 W
pojemność	12,9 l
zalecana objętość robocza	10 l
Rodzaj produktu	Ultradźwiękowe urządzenie do czyszczenia