



Ultradźwiękowe urządzenie do czyszczenia Elmasonic Select, Typ: 30



Dane zamówienia

Numer katalogowy

082000 30

GTIN

Klasa artykułu

04S

Opis

Wykonanie:

The ultrasonic cleaning devices from the Elmasonic Select series are powerful and individual.

- **5 ultrasonic modes.**
- **4 individual cleaning programs can be saved.**
- **Clear display showing all relevant cleaning parameters.**
- **Acoustic and visual feedback about the operating status.**
- **Tray made of drawn stainless steel**

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

pojemność: 27,5 l

długość urządzenia: 575 mm

szerokość urządzenia: 360 mm

długość kosza wsadowego: 455 mm

Szerokość kosza wsadowego: 250 mm

wysokość pojemnika do czyszczenia: 195 mm

Opis techniczny

moc grzewcza

1200 W

oznaczenie producenta	Select 300
szerokość urządzenia	360 mm
długość urządzenia	575 mm
wysokość pojemnika do czyszczenia	195 mm
napięcie znamionowe	220 - 240 V
długość kosza wsadowego	455 mm
Moc szczytowa ultradźwięków	1200 W
zasilanie energią	Zasilanie sieciowe
masa	12,2 kg
Szerokość kosza wsadowego	250 mm
pojemność	27,5 l
zalecana objętość robocza	22 l
Rodzaj produktu	Ultradźwiękowe urządzenie do czyszczenia