



Ultradźwiękowe urządzenie do czyszczenia Elmasonic Select, Typ: 90



Dane zamówienia

Numer katalogowy	082000 90
GTIN	
Klasa artykułu	04S

Opis

Wykonanie:

The ultrasonic cleaning devices from the Elmasonic Select series are powerful and individual.

- **5 ultrasonic modes.**
- **4 individual cleaning programs can be saved.**
- **Clear display showing all relevant cleaning parameters.**
- **Acoustic and visual feedback about the operating status.**
- **Tray made of drawn stainless steel**

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

pojemność: 89 l

długość urządzenia: 875 mm

szerokość urządzenia: 595 mm

długość kosza wsadowego: 545 mm

Szerokość kosza wsadowego: 460 mm

wysokość pojemnika do czyszczenia: 285 mm

Opis techniczny

Szerokość kosza wsadowego	460 mm
długość urządzenia	875 mm
szerokość urządzenia	595 mm
masa	43,4 kg
moc grzewcza	2000 W
Moc szczytowa ultradźwięków	3840 W
napięcie znamionowe	220 - 240 V
długość kosza wsadowego	545 mm
wysokość pojemnika do czyszczenia	285 mm
zasilanie energią	Zasilanie sieciowe
oznaczenie producenta	Select 900
pojemność	89 l
zalecana objętość robocza	63,7 l
Rodzaj produktu	Ultradźwiękowe urządzenie do czyszczenia