



## Ultradźwiękowe urządzenie do czyszczenia Elmasonic Select, Typ: 50



### Dane zamówienia

Numer katalogowy	082000 50
GTIN	
Klasa artykułu	04S

### Opis

#### Wykonanie:

The ultrasonic cleaning devices from the Elmasonic Select series are powerful and individual.

- **5 ultrasonic modes.**
- **4 individual cleaning programs can be saved.**
- **Clear display showing all relevant cleaning parameters.**
- **Acoustic and visual feedback about the operating status.**
- **Tray made of drawn stainless steel**

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

pojemność: 49,7 l

długość urządzenia: 775 mm

szerokość urządzenia: 425 mm

długość kosza wsadowego: 460 mm

Szerokość kosza wsadowego: 300 mm

wysokość pojemnika do czyszczenia: 290 mm

### Opis techniczny

szerokość urządzenia	425 mm
wysokość pojemnika do czyszczenia	290 mm
masa	30,4 kg
napięcie znamionowe	220 - 240 V
moc grzewcza	1600 W
zasilanie energią	Zasilanie sieciowe
Szerokość kosza wsadowego	300 mm
oznaczenie producenta	Select 500
długość urządzenia	775 mm
długość kosza wsadowego	460 mm
Moc szczytowa ultradźwięków	2160 W
pojemność	49,7 l
zalecana objętość robocza	40,3 l
Rodzaj produktu	Ultradźwiękowe urządzenie do czyszczenia