



Ultradźwiękowe urządzenie do czyszczenia Elmasonic xtra TT, Typ: 6



Dane zamówienia

Numer katalogowy

082001 6

GTIN

Klasa artykułu

04S

Opis

Wykonanie:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

Powerful ultrasonic cleaning by the Elmasonic xtra TT series for heavy-duty applications.

- **Greater ultrasonic effect due to selectable dynamic function.**
- **Integrated sweep function for uniform sound distribution in the cleaning bath.**
- **Visual limit temperature warning to protect sensitive parts.**
- **Individual timer and temperature control.**
- **Clearly arranged, splash-proof control panel.**

pojemność: 6,5 l

długość urządzenia: 420 mm

szerokość urządzenia: 250 mm

długość kosza wsadowego: 257 mm

Szerokość kosza wsadowego: 132 mm

wysokość pojemnika do czyszczenia: 150 mm

Opis techniczny

napięcie znamionowe

220 - 240 V

Szerokość kosza wsadowego	132 mm
długość urządzenia	420 mm
oznaczenie producenta	xtra TT 60H
zasilanie energią	Zasilanie sieciowe
szerokość urządzenia	250 mm
długość kosza wsadowego	257 mm
masa	10 kg
Moc szczytowa ultradźwięków	400 W
moc grzewcza	150 W
wysokość pojemnika do czyszczenia	150 mm
pojemność	6,5 l
zalecana objętość robocza	5 l