



Ultradźwiękowe urządzenie do czyszczenia Elmasonic xtra TT, Typ: 20



Dane zamówienia

Numer katalogowy

082001 20

GTIN

Klasa artykułu

04S

Opis

Wykonanie:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

Powerful ultrasonic cleaning by the Elmasonic xtra TT series for heavy-duty applications.

- **Greater ultrasonic effect due to selectable dynamic function.**
- **Integrated sweep function for uniform sound distribution in the cleaning bath.**
- **Visual limit temperature warning to protect sensitive parts.**
- **Individual timer and temperature control.**
- **Clearly arranged, splash-proof control panel.**

pojemność: 18 l

długość urządzenia: 420 mm

szerokość urządzenia: 390 mm

długość kosza wsadowego: 280 mm

Szerokość kosza wsadowego: 250 mm

wysokość pojemnika do czyszczenia: 200 mm

Opis techniczny

oznaczenie producenta	xtra TT 200H
moc grzewcza	300 W
napięcie znamionowe	220 - 240 V
Moc szczytowa ultradźwięków	1200 W
długość urządzenia	420 mm
zasilanie energią	Zasilanie sieciowe
szerokość urządzenia	390 mm
wysokość pojemnika do czyszczenia	200 mm
masa	13 kg
długość kosza wsadowego	280 mm
Szerokość kosza wsadowego	250 mm
pojemność	18 l
zalecana objętość robocza	13 l