



Ultradźwiękowe urządzenie do czyszczenia Elmasonic xtra TT, Typ: 3



Dane zamówienia

Numer katalogowy

082001 3

GTIN

Klasa artykułu

04S

Opis

Wykonanie:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

Powerful ultrasonic cleaning by the Elmasonic xtra TT series for heavy-duty applications.

- **Greater ultrasonic effect due to selectable dynamic function.**
- **Integrated sweep function for uniform sound distribution in the cleaning bath.**
- **Visual limit temperature warning to protect sensitive parts.**
- **Individual timer and temperature control.**
- **Clearly arranged, splash-proof control panel.**

pojemność: 3 l

długość urządzenia: 360 mm

szerokość urządzenia: 230 mm

długość kosza wsadowego: 196 mm

Szerokość kosza wsadowego: 112 mm

wysokość pojemnika do czyszczenia: 100 mm

Opis techniczny

zasilanie energią

Zasilanie sieciowe

moc grzewcza	140 W
Szerokość kosza wsadowego	112 mm
Moc szczytowa ultradźwięków	400 W
długość urządzenia	360 mm
oznaczenie producenta	xtra TT 30H
napięcie znamionowe	220 - 240 V
wysokość pojemnika do czyszczenia	100 mm
szerokość urządzenia	230 mm
długość kosza wsadowego	196 mm
masa	6 kg
pojemność	3 l
zalecana objętość robocza	2 l