



Ultradźwiękowe urządzenie do czyszczenia Elmasonic xtra TT, Typ: 12



Dane zamówienia

Numer katalogowy

082001 12

GTIN

Klasa artykułu

04S

Opis

Wykonanie:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

Powerful ultrasonic cleaning by the Elmasonic xtra TT series for heavy-duty applications.

- **Greater ultrasonic effect due to selectable dynamic function.**
- **Integrated sweep function for uniform sound distribution in the cleaning bath.**
- **Visual limit temperature warning to protect sensitive parts.**
- **Individual timer and temperature control.**
- **Clearly arranged, splash-proof control panel.**

pojemność: 14 l

długość urządzenia: 440 mm

szerokość urządzenia: 340 mm

długość kosza wsadowego: 262 mm

Szerokość kosza wsadowego: 222 mm

wysokość pojemnika do czyszczenia: 200 mm

Opis techniczny

oznaczenie producenta	xtra TT 120H
masa	11 kg
długość kosza wsadowego	262 mm
długość urządzenia	440 mm
szerokość urządzenia	340 mm
moc grzewcza	200 W
napięcie znamionowe	220 - 240 V
wysokość pojemnika do czyszczenia	200 mm
Szerokość kosza wsadowego	222 mm
Moc szczytowa ultradźwięków	800 W
zasilanie energią	Zasilanie sieciowe
pojemność	14 l
zalecana objętość robocza	10 l