



Latarka czołowa LED, Typ: HF8R-WORK



Dane zamówienia

Numer katalogowy	081391 HF8R-WORK
GTIN	
Klasa artykułu	04B

Opis

Wykonanie:

The Ledlenser HF8R Work is the robust flagship model for anyone who works in the dark. The standout feature is the patent-pending Adaptive Light Beam technology which allows automatic dimming and focusing. As a result, it is a hands-free head torch which requires no manual control at all. Virtually seamless focusing is delivered by the patent-pending Digital Advanced Focus System. In addition, the HF8R Work can be remotely controlled via the Ledlenser Connect app (upgrade with additional features available for a fee) and it impresses with its aluminium housing and protective elements on the front glass.

- **Automatic dimming and focusing thanks to the patent-pending Adaptive Light Beam technology for hands-free operation**
- **Powerful head torch with red front light and innovative Digital Advanced Focus System**
- **Extremely powerful rechargeable battery**
- **Protective elements on the front glass; waterproof if submerged continuously (IP68)**
- **Extensive scope of delivery provides varied attachment and usage options**

Opis techniczny

Napięcie akumulatorów	3,7 V
pojemność akumulatora	3,7 Ah
strumień światła, stopień 2	300 lm

zasięg	210 m
czas świecenia	90 h
Advanced Focus System (AFS)	tak
czas świecenia na stopniu 2	10 h
masa	198 g
strumień światła, stopień 3	900 lm
Oświetlenie przyciemniane	tak
kolor obudowy	czarny
rodzaj akumulatora	litowo-jonowy
czas świecenia na stopniu 3	3 h
zasilanie energią	Zasilanie sieciowe
z możliwością ponownego naładowania	tak
Liczba dołączonych baterii	1
stopień ochrony IP	IP 68
Strumień światła	20 lm
Strumień świetlny ze wzmacnieniem	1600 lm
Rodzaj produktu	Latarka czołowa