

PARAT®

Dados do pedido

Número do pedido	692540
GTIN	4006793801714
Classe de artigo	63X

Descrição

Modelo:

X-ABS is extremely impact resistant, tough and thus **suitable for air travel**. The surface is scratch-resistant, **non-slip (rubberised effect)** and **does not damage surfaces**. Double aluminium frame with **integral toggle cylinder locks**, positioning hinges with stop, and base studs.

1 base shell with cover board with sub-divisions, height 88 mm.

Internal fitments:

1 tool board with 25 shaft pockets and 1 securing pocket 400 mm, 1 tool board with 10 shaft pockets, 1 cover board with 15 shaft pockets and 1 securing pocket 400 mm and 1 document pocket with 2 business card pockets and 2 penholder slots.

TSA locks: When travelling to the USA these locks can be opened for searching and relocked by the US "Transportation Security Administration" (TSA) using a master key. Forcible opening of the case (irreparably damaging the locks) for searching can thus be avoided.

Descrição técnica

Dimensões interiores, comprimento	470 mm
Dimensões interiores, altura	360 mm

Dimensões interiores, largura	210 mm
Volume	35 l
Peso	6,8 kg
Material	X-ABS
Tipo de acondicionamento da ferramenta	bolsas porta-objetos
Capacidade de carga da mala	30 kg
Propriedades da mala	qualificado para voo
Tipo de produto	Sistema de transporte de ferramentas

Acessórios

Sortido de cadeados de combinação para reequipamento	692755
Tabuleiro de inserção com barra central, 6 barras pequenas e tampa	692770
Barra longitudinal para tabuleiros de base	692150
Tapete de proteção	692800