



Dados do pedido

Número do pedido	949613 4
GTIN	4067263642664
Classe de artigo	92S

Descrição

Modelo:

Garment locker with compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and label frame. With base.

With security twist bar lock; lockable with a padlock (not included in scope of delivery).

Ventilation concept: Air flows through holes in the rear of the cabinet floor ensuring good ventilation and drying within the compartment. Air infeed for special cabinets with fitted bases is via openings above the recessed base.

Norma:

DIN 4547

Descrição técnica

largura útil por compartimento	240 mm
Frentes do armário	Porta de dois batentes em chapa maciça
Altura	1950 mm
Modelo da estrutura inferior	Base

Modelo de fechadura	Fecho de trinco rotativo de segurança
Pintura especial possível	não
Número de compartimentos	4
Cobertura inclinada	não
para cadeado	sim
Profundidade	500 mm
Norma	DIN 4547
Profundidade da prateleira	477 mm
Número de prateleiras fixas	1
profundidade útil por compartimento	477 mm
altura útil por prateleira para chapéus	328 mm
Largura	1200 mm
para cadeado com Ø do aro até	6 mm
Número de varões para vestuário	1
altura útil por compartimento para vestuário	1420 mm
Placa de nome	não
Peso	68 kg
Aberturas de ventilação na porta	sim
Largura da prateleira	298 mm
Espessura do material	0,8 mm
Ângulo de abertura da porta	110 grau
Seleção da cor	RAL 7035, RAL 7016, RAL 5005
Tipo de produto	Cacifo