



Dados do pedido

Número do pedido	949615 3
GTIN	4067263642718
Classe de artigo	92S

Descrição

Modelo:

Garment locker with compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and label frame. With plastic feet.

With security twist bar lock; lockable with a padlock (not included in scope of delivery).

Ventilation concept: Air flows through holes in the rear of the cabinet floor ensuring good ventilation and drying within the compartment. Air infeed for special cabinets with fitted bases is via openings above the recessed base.

Norma:

DIN 4547

Descrição técnica

Norma	DIN 4547
Frentes do armário	Porta de dois batentes em chapa maciça
altura útil por compartimento para vestuário	1420 mm
Profundidade da prateleira	477 mm

Número de compartimentos	3
altura útil por prateleira para chapéus	328 mm
Largura da prateleira	298 mm
Profundidade	500 mm
Altura	1950 mm
Modelo da estrutura inferior	Pés de aço
Número de varões para vestuário	1
Número de prateleiras fixas	1
para cadeado com Ø do aro até	6 mm
Pintura especial possível	não
profundidade útil por compartimento	477 mm
Modelo de fechadura	Fecho de trinco rotativo de segurança
Peso	52 kg
largura útil por compartimento	240 mm
para cadeado	sim
Largura	900 mm
Aberturas de ventilação na porta	sim
Espessura do material	0,8 mm
Ângulo de abertura da porta	110 grau
Seleção da cor	RAL 7035, RAL 7016, RAL 5005
Tipo de produto	Cacifo