



Dados do pedido

Número do pedido	949631 3
GTIN	4067263642770
Classe de artigo	92S

Descrição

Modelo:

Garment locker with sloping roof attachment, which prevents objects from being left lying on top of the locker. Compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and label frame.

With base.

With security twist bar lock; lockable with a padlock (not included in scope of delivery).

Norma:

DIN 4547

Descrição técnica

Aberturas de ventilação na porta	sim
Modelo de fechadura	Fecho de trinco rotativo de segurança
Frentes do armário	Porta de dois batentes em chapa maciça
Modelo da estrutura inferior	Base
Cobertura inclinada	sim
altura útil por prateleira para chapéus com cobertura inclinada	328 mm
Peso	57 kg
altura útil por compartimento para vestuário	1420 mm
Largura da prateleira	298 mm
profundidade útil por compartimento	477 mm
Número de prateleiras fixas	1

Profundidade	500 mm
Altura atrás	2180 mm
Norma	DIN 4547
para cadeado	sim
Profundidade da prateleira	477 mm
Pintura especial possível	não
Altura à frente	1950 mm
largura útil por compartimento	240 mm
para cadeado com Ø do aro até	6 mm
Largura	900 mm
Número de varões para vestuário	1
Número de compartimentos	3
Espessura do material	0,8 mm
Ângulo de abertura da porta	110 grau
Seleção da cor	RAL 7035, RAL 7016, RAL 5005
Tipo de produto	Cacifo