



## Dados do pedido

Número do pedido	949631 2
GTIN	4067263642763
Classe de artigo	92S

## Descrição

### Modelo:

Garment locker with sloping roof attachment, which prevents objects from being left lying on top of the locker. Compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and label frame.

With base.

With security twist bar lock; lockable with a padlock (not included in scope of delivery).

### Norma:

**DIN 4547**

## Descrição técnica

largura útil por compartimento	240 mm
Número de compartimentos	2
altura útil por prateleira para chapéus com cobertura inclinada	328 mm
Altura à frente	1950 mm
altura útil por compartimento para vestuário	1420 mm

Pintura especial possível	não
para cadeado	sim
Número de prateleiras fixas	1
Profundidade da prateleira	477 mm
para cadeado com Ø do aro até	6 mm
profundidade útil por compartimento	477 mm
Norma	DIN 4547
Frentes do armário	Porta de dois batentes em chapa maciça
Largura da prateleira	298 mm
Altura atrás	2180 mm
Modelo da estrutura inferior	Base
Número de varões para vestuário	1
Aberturas de ventilação na porta	sim
Modelo de fechadura	Fecho de trinco rotativo de segurança
Profundidade	500 mm
Largura	600 mm
Cobertura inclinada	sim
Peso	42 kg
Espessura do material	0,8 mm
Ângulo de abertura da porta	110 grau
Seleção da cor	RAL 7035, RAL 7016, RAL 5005
Tipo de produto	Cacifo