



Dados do pedido

Número do pedido	949633 3
GTIN	4067263642831
Classe de artigo	92S

Descrição

Modelo:

Garment locker with sloping roof attachment, which prevents objects from being left lying on top of the locker. Compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and label frame.

With plastic feet.

With security twist bar lock; lockable with a padlock (not included in scope of delivery).

Norma:

DIN 4547

Descrição técnica

Profundidade	500 mm
Aberturas de ventilação na porta	sim
para cadeado com Ø do aro até	6 mm
Modelo de fechadura	Fecho de trinco rotativo de segurança
Peso	57 kg
Largura	900 mm
Altura à frente	1950 mm
altura útil por compartimento para vestuário	1420 mm
profundidade útil por compartimento	477 mm
Norma	DIN 4547
Frentes do armário	Porta de dois batentes em chapa maciça
Cobertura inclinada	sim

Número de prateleiras fixas	1
Número de varões para vestuário	1
Altura atrás	2180 mm
altura útil por prateleira para chapéus com cobertura inclinada	328 mm
Largura da prateleira	298 mm
Modelo da estrutura inferior	Pés de aço
Profundidade da prateleira	477 mm
largura útil por compartimento	240 mm
Pintura especial possível	não
Número de compartimentos	3
para cadeado	sim
Espessura do material	0,8 mm
Ângulo de abertura da porta	110 grau
Seleção da cor	RAL 7035, RAL 7016, RAL 5005
Tipo de produto	Cacifo