



## Dados do pedido

Número do pedido	949633 2
GTIN	4067263642824
Classe de artigo	92S

## Descrição

### Modelo:

Garment locker with sloping roof attachment, which prevents objects from being left lying on top of the locker. Compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and label frame.

With plastic feet.

With security twist bar lock; lockable with a padlock (not included in scope of delivery).

### Norma:

**DIN 4547**

## Descrição técnica

Altura atrás	2180 mm
Número de prateleiras fixas	1
para cadeado	sim
Cobertura inclinada	sim
Número de varões para vestuário	1
Largura	600 mm

para cadeado com Ø do aro até	6 mm
Número de compartimentos	2
Largura da prateleira	298 mm
Altura à frente	1950 mm
Modelo de fechadura	Fecho de trinco rotativo de segurança
largura útil por compartimento	240 mm
Profundidade	500 mm
Peso	42 kg
profundidade útil por compartimento	477 mm
Profundidade da prateleira	477 mm
Frentes do armário	Porta de dois batentes em chapa maciça
altura útil por prateleira para chapéus com cobertura inclinada	328 mm
Modelo da estrutura inferior	Pés de aço
Pintura especial possível	não
Aberturas de ventilação na porta	sim
Norma	DIN 4547
altura útil por compartimento para vestuário	1420 mm
Espessura do material	0,8 mm
Ângulo de abertura da porta	110 grau
Seleção da cor	RAL 7035, RAL 7016, RAL 5005
Tipo de produto	Cacifo