



Dados do pedido

Número do pedido	640288 1/2
GTIN	4018754336388
Classe de artigo	63A

Descrição

Modelo:

Fixing is performed by the locking ring. With reversing lever for right-hand and left-hand threads. Convenient, simple and fast adjustment of the lengths using a rocker switch, even one-handed. Five latch steps with extension lengths of 410 mm, 465 mm, 520 mm, 575 mm and 630 mm. Maximum permissible torque 512 Nm.

Material selection and special forging process guarantee optimal functioning and long life.

Norma:

Außenvierkant nach **DIN 3120-A 12,5** mit federnder Kugel.

Descrição técnica

Quadrado de acionamento	1/2 polegada
Norma	DIN 3122
comprimento total	410 - 630 mm
Número de dentes	36
Ângulo de trabalho	10 grau
Material	Chrome-Alloy-Steel
Superfície	cromado
com extrator	não
Cabeça do roquete separável do punho	não
Punho rotativo	não
de extração contínua	não
Orifício de alojamento na extremidade do cabo	não

Tipo de producto

Roquete