



Dados do pedido

Número do pedido	754890 35
GTIN	4016134010309
Classe de artigo	73V

Descrição

Modelo:

Combined **engineer's hammer and soft hammer**, sides additionally with ground striking faces for working in confined spaces. Head made of highly tempered steel with an exchangeable set of inserts made of wear-resistant nylon – shore hardness approx. 68D. With unbreakable **Ultratec** glass fibre handle.

Descrição técnica

Material do cabo	Fibra de vidro
Comprimento total	324 mm
Comprimento da cabeça com insertos	114 mm
Série	Ultratec DUO
Dimensões da cabeça do martelo	34×34 mm
Peso	0,66 kg
Material da caixa	Aço para melhoramento, temperado por indução
Material do inserto	Nylon, branco, duro (de um lado)
Ø da cabeça do martelo	35 mm
sem ricochete	não
Tipo de produto	Martelo

Acessórios

Inserto sobresselente em nylon Ø da cabeça do martelo 35

754895 35