



Dados do pedido

Número do pedido	754890 40
GTIN	4016134010316
Classe de artigo	73V

Descrição

Modelo:

Combined **engineer's hammer and soft hammer**, sides additionally with ground striking faces for working in confined spaces. Head made of highly tempered steel with an exchangeable set of inserts made of wear-resistant nylon – shore hardness approx. 68D. With unbreakable **Ultratec** glass fibre handle.

Descrição técnica

Dimensões da cabeça do martelo	38×38 mm
Material do cabo	Fibra de vidro
Comprimento da cabeça com insertos	124 mm
Série	Ultratec DUO
Peso	1 kg
Material do inserto	Nylon, branco, duro (de um lado)
Material da caixa	Aço para melhoramento, temperado por indução
Comprimento total	357 mm
Ø da cabeça do martelo	40 mm
sem ricochete	não
Tipo de produto	Martelo

Acessórios

Inserto sobresselente em nylon Ø da cabeça do martelo 40

754895 40