



Dados do pedido

Número do pedido	082002 160
GTIN	4250004100350
Classe de artigo	04S

Descrição

Modelo:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

Elmasonic xtra ST is the ultrasonic device for the most severe dirt and is particularly suitable for extremely demanding applications in the field of industrial cleaning.

- **2 selectable ultrasonic frequencies (25 kHz for the most stubborn dirt and 45 kHz for gentle cleaning).**
- **Integrated sweep function for even sound distribution in the cleaning bath.**
- **Selectable pulse function increases the ultrasonic peak power.**
- **Dynamic function (ultrasonic power can be increased temporarily by up to 20%).**
- **Sturdy tray made from welded stainless steel.**

Descrição técnica

Comprimento do cesto de encaixe	480 mm
Largura do cesto de encaixe	525 mm

Tensão nominal	400 V
Potência de aquecimento	7500 W
Comprimento do aparelho	935 mm
Alimentação de energia	A energia elétrica
Designação do fabricante	xtra ST 1600H
Peso	93 kg
Altura do tanque de depuração	415 mm
Excelente desempenho por ultrassons	7200 W
Largura do aparelho	865 mm
Volume	156,3 l
volume de trabalho recomendado	133 l
Tipo de produto	Aparelho de limpeza por ultrassons

Acessórios

Cesto de encaixextra ST 160	082103 160
Tampa de isolamento acústicoextra ST 160	082105 160