



Dados do pedido

Número do pedido	082002 250
GTIN	4250004100367
Classe de artigo	04S

Descrição

Modelo:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

Elmasonic xtra ST is the ultrasonic device for the most severe dirt and is particularly suitable for extremely demanding applications in the field of industrial cleaning.

- **2 selectable ultrasonic frequencies (25 kHz for the most stubborn dirt and 45 kHz for gentle cleaning).**
- **Integrated sweep function for even sound distribution in the cleaning bath.**
- **Selectable pulse function increases the ultrasonic peak power.**
- **Dynamic function (ultrasonic power can be increased temporarily by up to 20%).**
- **Sturdy tray made from welded stainless steel.**

Descrição técnica

Altura do tanque de depuração	485 mm
Alimentação de energia	A energia elétrica

Largura do cesto de encaixe	630 mm
Comprimento do aparelho	1080 mm
Potência de aquecimento	7500 W
Designação do fabricante	xtra ST 2500H
Peso	107 kg
Largura do aparelho	915 mm
Excelente desempenho por ultrassons	8000 W
Comprimento do cesto de encaixe	575 mm
Tensão nominal	400 V
Volume	245,1 l
volume de trabalho recomendado	215 l
Tipo de produto	Aparelho de limpeza por ultrassons

Acessórios

Cesto de encaixextra ST 250	082103 250
Tampa de isolamento acústicoextra ST 250	082105 250