



## Dados do pedido

Número do pedido	082002 60
GTIN	4250004100343
Classe de artigo	04S

## Descrição

### Modelo:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

Elmasonic xtra ST is the ultrasonic device for the most severe dirt and is particularly suitable for extremely demanding applications in the field of industrial cleaning.

- **2 selectable ultrasonic frequencies (25 kHz for the most stubborn dirt and 45 kHz for gentle cleaning).**
- **Integrated sweep function for even sound distribution in the cleaning bath.**
- **Selectable pulse function increases the ultrasonic peak power.**
- **Dynamic function (ultrasonic power can be increased temporarily by up to 20%).**
- **Sturdy tray made from welded stainless steel.**

## Descrição técnica

Altura do tanque de depuração	330 mm
Comprimento do aparelho	825 mm

Tensão nominal	400 V
Largura do aparelho	595 mm
Alimentação de energia	A energia elétrica
Comprimento do cesto de encaixe	415 mm
Largura do cesto de encaixe	255 mm
Designação do fabricante	xtra ST 600H
Potência de aquecimento	1400 W
Peso	55 kg
Excelente desempenho por ultrassons	3600 W
Volume	56,3 l
volume de trabalho recomendado	45 l
Tipo de produto	Aparelho de limpeza por ultrassons

---

## Acessórios

Tampa de isolamento acústico xtra ST 60	082105 60
Cesto de encaixe xtra ST 60	082103 60