

**Garant**

## Dados do pedido

Número do pedido	706001 300
GTIN	4067263031468
Classe de artigo	71B

## Descrição

### Modelo:

Box joint designed to prevent fingers being trapped. Push-button **fine step adjustment**, which also allows for quick adjustments directly on the workpiece. Concave profile serrated jaws, self-clamping. The teeth also run against each other in the rear of the jaw for a tight grip. Surface manganese phosphated, polished teeth. Ergonomically shaped handles with non-slip plastic coating.

### Norma:

**DIN ISO 8976**

## Descrição técnica

Largura de aperto para tubos	2.3/4 polegada
Largura de aperto para sextavado	60 mm
comprimento total	300 mm
Número de posições de encaixe de ajuste preciso	30
Superfície	mordentes polidos, com fosfato de manganês
Norma	DIN ISO 8976
Modelo do mordente	mordentes de fixação dentados, serrilhados
Material	Aço cromo-vanádio
não produz faíscas	não

Ajuste rápido	sim
Possibilidade de regulação precisa do encaixe	sim
Fixação automática	sim
Proteção contra travamento	sim
Tipo de produto	Chave para tubos e canalização