

Garant

Dados do pedido

Número do pedido	964450 100X135
GTIN	4067263476771
Classe de artigo	9GM

Descrição

Modelo:

Industrial workplace mat for medium to heavy-duty requirements. The ergonomic rubber mat is suitable for dry and wet walking and standing workplaces. The mat surface has an optimally coordinated pivot point and very good slip resistance and position stability. Bevelled edges on all sides to avoid the risk of stumbling. Very easy-to-clean surface with light-reflecting properties. The oil-resistant floor mat has a fire protection class Bfl-s1.

Due to the elastic properties of the rubber compound and the special geometry on the rear, the mat has a particularly shock-absorbing and activating effect and protects against unhealthy levels of coldness. Durable mat suitable for multi-shift operation.

Electrically dissipative, surface resistance of less than $10^7 \Omega$. The mat is marked with an ESD safety label.

Norma:

DIN EN 61340-4-1

Descrição técnica

Espessura	16 mm
Material	Borracha nitrílica (NBR)
Peso	20 kg
Largura	100 cm
Comprimento	135 cm
Classe de proteção contra incêndio	Bfl-s1

Dureza conforme Shore A	55
Conforto em pé	Antifadiga
Conforto em pé	Antiderrapante
Conforto em pé	Isolamento (temperatura)
Proteção contra choques	Piso
Propriedades do material	resistente a óleo
Propriedades do material	altamente inflamável
Propriedade eletrostática	EGB/ESD
Cor	cinzento escuro manchado
Tipo de produto	Tapete para posto de trabalho