

Garant**Dados do pedido**

Número do pedido	920312 1500
GTIN	4067263736202
Classe de artigo	91S

Descrição**Modelo:**

Base frame with anodised aluminium lift unit. With cross bracing for stabilisation. 50 mm thick worktop made of beech marine ply. Stepless height adjustment from 740 – 1140 mm, quickly and easily selected using the control panel. Control panel with memory function for 3 different working heights.

Descrição técnica

Material do tampo de trabalho	Multiplex de faia
Profundidade	750 mm
Regulação de altura contínua	sim
Tipo de conector de entrada	F
Espessura do tampo de trabalho	50 mm
Princípio da regulação de altura	montagem completa
Faixa de regulação da altura (aresta superior do tampo de trabalho) de – até	740 - 1140 mm
Profundidade do tampo de trabalho	750 mm
Alimentação de energia	A energia elétrica

capacidade de carga máxima	500 kg
Tensão de ligação	250 V
Largura	1500 mm
Comprimento do tampo de trabalho	1500 mm
Superfície do tampo de trabalho	lacado incolor
Capacidade de carga sob esforço permanente	350 kg
Peso	75 kg
Capacidade de carga da bancada de trabalho/mesa – carga máxima da prateleira distribuída por toda a superfície (em madeira)	500 kg
Modelo de regulação de altura	elétrico
Espessura do tampo	50 mm
Compensação de altura	25 mm
Tipo de produto	Bancada de trabalho