

RUNPOTEC
HPI KABELNENZIEHSPEZIALIST

Dados do pedido

Número do pedido	814869 30
GTIN	9120045477122
Classe de artigo	86A

Descrição

Modelo:

3 mm thick fibreglass rod **accepts pushing force** yet is **highly flexible**; ideal for pulling cables into complicated runs where conduit is already laid or where there are many bends in the conduit.

Ergonomic holding and carrying handle. Patented guiding head with anti-twist and kink protection (2 pcs. external thread Ø RTG 6 mm). Automatic glide back protection. Anti-slip coating. Suitable for construction sites, splash-proof and dust-proof, shock-proof and break-proof. Possible up to a radius of 38 mm.

Also compatible with RUNPOCAM RC2 (No. 814878) and the basalt rods (No. 814877).

With integrated digital meter counter.

Descrição técnica

Comprimento da fita	30 m
Carga máxima da ligação guia passa-cabos – casquilho	1,3 kN
Carga máxima da guia passa-cabos	4,5 kN
Tipo de produto	Ferramenta para enrolador de cabo

