



Dados do pedido

Número do pedido	713501 160
GTIN	4003773016007
Classe de artigo	73F

Descrição

Modelo:

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for cutting hard and soft wire. Serrated inside jaws.

Pliers, chrome-plated, handles with ergonomically optimised multi-component covers and KNIPEXtend interface.

KNIPEXtend is used to connect extensions, such as ColourCode Clips (CCCs) for customisation or TetheredTool Clips (TTCs) for attaching a Tethered Tools fall protection device.

Norma:

DIN ISO 5745

Descrição técnica

comprimento total	160 mm
Comprimento do mordente	50 mm
Forma da boca	oval/pontiagudo, angulado (40° – 45°)
Norma	DIN ISO 5745
Propriedades do mordente	Arestas de corte temperadas por indução (aprox. 60 HRC)
Modelo do mordente	interior rugoso
Punho	Manga multicomponente
Material	Aço cromo-vanádio, forjado por estampagem e temperado a óleo
Superfície	cromado

Tipo de producto

Alicates multifuncional