



Dados do pedido

| | |
|------------------|---------------|
| Número do pedido | 724861 125 |
| GTIN | 4003773039501 |
| Classe de artigo | 73F |

Descrição

Modelo:

Slim shape with induction hardened cutting edges (approx. 62 HRC).

Pliers chrome-plated, handles with multi-component covers and KNIPEXtend interface.

KNIPEXtend is used to connect extensions, such as ColourCode Clips (CCCs) for customisation or TetheredTool Clips (TTCs) for attaching a Tethered Tools fall protection device.

Norma:

DIN ISO 5749

Descrição técnica

| | |
|---|---|
| comprimento total | 125 mm |
| Potência de corte de fio duro até Ø | 1,5 mm |
| Potência de corte de fio macio até Ø | 3 mm |
| Norma | DIN ISO 5749 |
| Punho | Manga multicomponente |
| Método de produção | Arestas de corte temperadas por indução (aprox. 62 HRC) |
| Superfície | cromado |
| Alicate de corte lateral de alto desempenho | não |
| com mola de abertura ativável | não |
| Tipo de produto | Alicate cortante |

