



## Dados do pedido

Número do pedido	724861 140
GTIN	4003773039488
Classe de artigo	73F

## Descrição

### Modelo:

Slim shape with induction hardened cutting edges (approx. 62 HRC).

Pliers chrome-plated, handles with multi-component covers and KNIPEXtend interface.

KNIPEXtend is used to connect extensions, such as ColourCode Clips (CCCs) for customisation or TetheredTool Clips (TTCs) for attaching a Tethered Tools fall protection device.

### Norma:

**DIN ISO 5749**

## Descrição técnica

comprimento total	140 mm
Potência de corte de fio duro até Ø	1,8 mm
Potência de corte de fio macio até Ø	4 mm
Norma	DIN ISO 5749
Punho	Manga multicomponente
Método de produção	Arestas de corte temperadas por indução (aprox. 62 HRC)
Superfície	cromado
Alicate de corte lateral de alto desempenho	não
com mola de abertura ativável	não
Tipo de produto	Alicate cortante

