

Garant

Dados do pedido

| | |
|------------------|---------------|
| Número do pedido | 860492 300 |
| GTIN | 4067263743002 |
| Classe de artigo | 81D |

Descrição

Modelo:

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Smooth running steel spindle with trapezoidal thread, burnished.

Moving jaw with integral **spindle locking prevents the release** of the spindle even in case of vibrations. Maximum force transfer due to **power grip** with easy-grip Haptoprene surface and impact-resistant PP core. Surface structure is anti-slip even with wet, oily hands.

All-steel clamp with fold-out handle. Quick approach and clamping of the workpiece with the handle engaged in the vertical position. **Powerful and convenient working with the handle folded out.**

Descrição técnica

| | |
|---------------------------------|----------|
| Alcance | 140 mm |
| Largura de aperto | 300 mm |
| Secção transversal da corrediça | 25×12 mm |
| Tipo de produto | Grampo |

