

Garant

Dados do pedido

Número do pedido	860492 400
GTIN	4067263743026
Classe de artigo	81D

Descrição

Modelo:

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Smooth running steel spindle with trapezoidal thread, burnished.

Moving jaw with integral **spindle locking prevents the release** of the spindle even in case of vibrations. Maximum force transfer due to **power grip** with easy-grip Haptoprene surface and impact-resistant PP core. Surface structure is anti-slip even with wet, oily hands.

All-steel clamp with fold-out handle. Quick approach and clamping of the workpiece with the handle engaged in the vertical position. **Powerful and convenient working with the handle folded out.**

Descrição técnica

Secção transversal da corrediça	25×12 mm
Alcance	120 mm
Largura de aperto	400 mm
Tipo de produto	Grampo

