

**Honeywell****Dados do pedido**

Número do pedido	094797 7
GTIN	13603835714117
Classe de artigo	04Q

**Descrição****Modelo:**

**Flextril™ 211.** Nitrile chemical protection gloves with **light cut protection**. With integrated Honeywell Moisture Dispersion Technology for high wearing comfort. High finger mobility and excellent grip thanks to the Flextril™ coating. The QR code on the back of the hand provides easy and quick access to all important technical documents and specifications. Approved for contact with foodstuffs.

Category III safety gloves.

**Descrição técnica**

Série	Flextril™
Tipo de luvas	Luvas de proteção química
Designação do fabricante	Flextril™ 211
Espessura da parede	1,3 mm
Tamanho das luvas	7
Propriedades das luvas	Certificação para produtos alimentares

Classe de proteção	Proteção contra riscos bacteriológicos conforme EN 374
EN 374	Tipo A (JKMOPT)
Resistência a produtos químicos	JKMOPT
EN 388	4X21A
EN 407	X1XXXX
Material	Nitrilo
material de suporte	Nitrilo
AQL	0,65
Comprimento	350 mm
Espessura	1,3 mm
Cor	cinzento/azul
Utilização	reutilizável
Norma/regulamento	EN 374
Tipo de produto	Luvas de proteção química