

Honeywell**Dados do pedido**

Número do pedido	094798 11
GTIN	13603835714070
Classe de artigo	04Q

Descrição**Modelo:**

Flextril™ 231. Nitrile chemical protection gloves with **medium-high cut protection**. With integrated Honeywell Moisture Dispersion Technology for high wearing comfort. High finger mobility and excellent grip thanks to the Flextril™ coating. The QR code on the back of the hand provides easy and quick access to all important technical documents and specifications. Approved for contact with foodstuffs. Category III safety gloves.

Descrição técnica

Tipo de luvas	Luvas de proteção química
Designação do fabricante	Flextril™ 231
Espessura da parede	1,7 mm
Tamanho das luvas	11
Série	Flextril™
Propriedades das luvas	Certificação para produtos alimentares

Classe de proteção	Proteção contra riscos bacteriológicos conforme EN 374
EN 374	Tipo A (JKMOPT)
Resistência a produtos químicos	JKMOPT
EN 388	4X32C
EN 407	X1XXXX
Material	Nitrilo
material de suporte	Nitrilo
AQL	0,65
Comprimento	320 mm
Espessura	1,7 mm
Cor	cinzento/azul
Utilização	reutilizável
Classe de proteção contra o corte	C
Norma/regulamento	EN 374
Tipo de produto	Luvas de proteção química