



Dados do pedido

Número do pedido	077111 7222906023
GTIN	4014586900346
Classe de artigo	03F

Descrição

Modelo:

FEIN – Compact angle grinder Ø 125 mm.

- **Robust, powerful motor for everyday use.**
- **High level of protection for the user thanks to recoil monitoring, restart inhibit and anti-vibration handle.**
- **High overload capability thanks to direct motor cooling; grinding head can be rotated in 90° steps (optimum switch position for the application).**
- **Grinding media can be changed quickly without the need for tools thanks to the quick-release clamping nut.**

Descrição técnica

Comprimento do cabo	4 m
profundidade de corte máxima	35 mm
vibração máxima conforme EN	6 m/s ²
Comutação de homem morto	não
n.º máximo de rotações	11500 r,p,m,
Alimentação de energia	A energia elétrica
Peso	2,4 kg

Frequência de rede	50 Hz
Designação do fabricante	CG17-125
Particularidade	formato curto
Arranque suave	sim
Ø máximo do disco	125 mm
Bloqueio contra re arranque	sim
Tensão de rede	230 V
Consumo energético	1700 W
Tipo de produto	Retificadora angular