



## Dados do pedido

Número do pedido	296605 10
GTIN	4045197519481
Classe de artigo	22E

## Descrição

### Modelo:

**Carbide** – steel shanks with 700 - 800 N/mm<sup>2</sup> strength and flat chamfered mounting surface. Fitted with diamond ground carbide inserts. Angles on the inserts are precision ground. All turning tools are supplied with sharp cutting edges. Sharpening the cutting edge with a boron carbide hand lapper will increase the tool edge life. The extent of the wear area is dependent on the cutting conditions. For roughing and interrupted machining it is imperative that the cutting edges are sharpened.

Fitted with diamond ground carbide inserts.

## Descrição técnica

Largura da aresta de corte	10 mm
Altura da haste	10 mm
Comprimento total	90 mm
Largura da haste b	10 mm
Óleo de corte	P20/K25
Tipo de produto	Ferramenta de torneiar