



Dados do pedido

Número do pedido	297175 16
GTIN	4045197521453
Classe de artigo	22E

Descrição

Modelo:

Carbide – steel shanks with 700 - 800 N/mm² strength and flat chamfered mounting surface. Fitted with diamond ground carbide inserts. Angles on the inserts are precision ground. All turning tools are supplied with sharp cutting edges. Sharpening the cutting edge with a boron carbide hand lapper will increase the tool edge life. The extent of the wear area is dependent on the cutting conditions. For roughing and interrupted machining it is imperative that the cutting edges are sharpened.

Fitted with diamond ground carbide inserts.

Descrição técnica

para furos de Ø a partir de	36 mm
Quadrado da haste	16 mm
Comprimento total	180 mm
Óleo de corte	P20/K25
Tipo de produto	Ferramenta de torneiar