


FAHRION®
FAHREYOND FINESSION

Dados do pedido

Número do pedido	309550 10
GTIN	2050001704559
Classe de artigo	39Y

Descrição

Modelo:

Spring steel, through hardened and ground. The through bore (longer clamping range than DIN collets) increases the clamping force. More slits than DIN collets, giving a greater insertion depth in the collet chuck. Suitable for jobber drills, for clamping on the guide land **Clamping range = Nominal size down to minus 0.5 mm.** 5 or 6 slits each end.

Descrição técnica

Ø de fixação nominal d	10 mm
para mandril	2 - 25 mm
Atributo do nome do produto	2 # 25 mm
Norma	ISO 10897
Tipo	462 E
Ø exterior D	35,05 mm
Comprimento total L	52 mm
Tipo de produto	Pinça de aperto

