


**FAHRION®**  
FAHREYOND FINESSION

## Dados do pedido

Número do pedido	309560 10
GTIN	2050001704719
Classe de artigo	39Y

## Descrição

### Modelo:

Spring steel, through hardened and ground. The through bore (longer clamping range than DIN collets) increases the clamping force. More slits than DIN collets, giving a greater insertion depth in the collet chuck. Suitable for jobber drills, for clamping on the guide land **Clamping range = Nominal size down to minus 0.5 mm.** 5 or 6 slits each end.

## Descrição técnica

Ø de fixação nominal d	10 mm
para mandril	4 - 32 mm
Atributo do nome do produto	4 # 32 mm
Norma	ISO 10897
Tipo	467 E
Ø exterior D	43,7 mm
Comprimento total L	60 mm
Tipo de produto	Pinça de aperto

