

**Garant**

## Dados do pedido

Número do pedido	468790 150/1
GTIN	4045197519238
Classe de artigo	41H

## Descrição

### Modelo:

Sturdy housing of high quality special casting; Vee base with ground contact surfaces in the angle (important for marking out, aligning, etc.). All measuring faces are exactly parallel to the axis of the vial. One longitudinal and one transverse vial each of glass. With insulated handles on the housing and protective glass over the vials.

### Adjustment of the longitudinal vial:

An adjustment screw allows the longitudinal vial to be reset to the 0 position easily and without play, with no need for disassembly.

### Norma:

**DIN 877**

## Descrição técnica

Largura palmilha	40 mm
Classe de precisão	1
Comprimento da palmilha	150 mm
Leitura	0,02 mm/m
Norma	DIN 877
embalagem	caixa estável
Calibração	H2

Tipo de produto

Nível de bolha de ar

**Prestações de serviços**Calibração Nível de água para eixos / inclinómetro  
eletrónico Precisão 0,02

026620 0,02