

STIEFELMAYER



Dados do pedido

| | |
|------------------|---------------|
| Número do pedido | 468800 300/1 |
| GTIN | 4045197207128 |
| Classe de artigo | 46R |

Descrição

Modelo:

Sturdy housing of high quality special casting; hammer finish. Vee and flat base with precision-ground contact surfaces in the angle (important for marking out, aligning, etc.). All measuring faces are exactly parallel to the axis of the vial. One longitudinal and one transverse vial each of glass. With insulated handles on the housing and protective glass over the vials.

Norma:

DIN 877

Descrição técnica

| | |
|-------------------------|----------------------|
| Leitura | 0,02 mm/m |
| Comprimento da palmilha | 300 mm |
| Largura palmilha | 50 mm |
| Classe de precisão | 1 |
| Norma | DIN 877 |
| embalagem | caixa estável |
| Calibração | H2 |
| Tipo de produto | Nível de bolha de ar |

Prestações de serviços

026620 0,02

Calibração Nível de água para eixos / inclinómetro
eletrónico Precisão 0,02

