

Garant

Dados do pedido

Número do pedido	468790 200/1
GTIN	4045197519214
Classe de artigo	41H

Descrição

Modelo:

Sturdy housing of high quality special casting; Vee base with ground contact surfaces in the angle (important for marking out, aligning, etc.). All measuring faces are exactly parallel to the axis of the vial. One longitudinal and one transverse vial each of glass. With insulated handles on the housing and protective glass over the vials.

Adjustment of the longitudinal vial:

An adjustment screw allows the longitudinal vial to be reset to the 0 position easily and without play, with no need for disassembly.

Norma:**DIN 877**

Descrição técnica

Classe de precisão	1
Comprimento da palmilha	200 mm
Largura palmilha	40 mm
Leitura	0,02 mm/m
Norma	DIN 877
embalagem	caixa estável
Calibração	H2

Tipo de produto

Nível de bolha de ar

Prestações de serviçosCalibração Nível de água para eixos / inclinómetro
eletrónico Precisão 0,02

026620 0,02