

Garant

Dados do pedido

Número do pedido	469190 150/2
GTIN	4045197519245
Classe de artigo	41H

Descrição

Modelo:

Sturdy frame of high quality special casting; hammer finish. 3 sides Vee ground, 1 side flat. One longitudinal and one transverse vial each of glass. The sensitivity (scale value) of the longitudinal vial is specified on the square. Accuracy grade 1 has insulated handles on the housing and protective glass cover over the vials.

Adjustment of the longitudinal vial:

An adjustment screw allows the longitudinal vial to be reset to the 0 position easily and without play, with no need for disassembly.

Norma:

DIN 877

Descrição técnica

Comprimento da palmilha	150 mm
Largura palmilha	40 mm
Leitura	0,1 mm/m
Classe de precisão	2
Norma	DIN 877

embalagem	caixa estável
Calibração	H1
Tipo de produto	Nível de bolha de ar

Prestações de serviços

CalibraçãoNível de água de quadro Precisão 0,10	026600 0,10
-------------------------------------------------	-------------