

STIEFELMAYER



Dados do pedido

Número do pedido	468800 160/2
GTIN	4028126003503
Classe de artigo	46R

Descrição

Modelo:

Sturdy housing of high quality special casting; hammer finish. Vee and flat base with precision-ground contact surfaces in the angle (important for marking out, aligning, etc.). All measuring faces are exactly parallel to the axis of the vial. One longitudinal and one transverse vial each of glass. With insulated handles on the housing and protective glass over the vials.

Norma:

DIN 877

Descrição técnica

Leitura	0,1 mm/m
Classe de precisão	2
Comprimento da palmilha	160 mm
Largura palmilha	40 mm
Norma	DIN 877
embalagem	caixa estável
Calibração	H2
Tipo de produto	Nível de bolha de ar

Prestações de serviços

026620 0,10

Calibração Nível de água para eixos / inclinómetro
eletrónico Precisão 0,10

